



Dimension Charts for Advanced Rolling Steel Doors: RapidSlat® Models 611/621/626

Please be advised that the dimensions provided below are approximations based on standard offerings. If options are added or sideroom and headroom clearances are tight on your projects, please be sure to work with the factory for the most accurate data based on your jobs needs.

Models 611/621/626 Face of Wall Mounted

Slat Data

Model	Slat	Opening Width	Standard	Optional
611	C187*	Up to 15'4"	22 ga.	20,18 ga. or 22,20 ga. ss or .04" (18 ga.) Aluminum
611	C275	Up to 20'0"	22 ga.	20,18 ga. or 22,20 ga. ss or .05" (16 ga.) Aluminum
611	F265	Up to 20'0"	22 ga.	20,18 ga. or 22,20 ga. ss or .05" (16 ga.) Aluminum
621	F265	Up to 20'0"	22 ga.	20,18 ga. or 22,20 ga. ss or .05" (16 ga.) Aluminum
				Front of slat: 22,20,18 ga. or 22,20 ga. ss or .05" (18 ga.) Aluminum
				Back of slat: 24,22 ga. or 22 ga. ss; .025" (22 ga.)
626	F265i	Up to 20'0"	24/24 ga.	Aluminum

*C-187 slat limited to 15'4" in width.

NOTE: 18 ga. C275 and F265 slat profiles on Model 611 are available with full fenestration or partial curtain fenestration

Slats are galvanized and painted steel, stainless steel (ss) or aluminum.

Slat	R-value	U-value	STC Rating
F265i	7.7	0.13	21

Headroom Clearance Dimensions

Slat	Opening Height	Dimension A	Max Door Opening Width
C187	Thru 8'0"	14"	15'4"
C187	Thru 14'0"	16"	15'4"
C187	Thru 20'0"	18"	15'4"
C275	Thru 5'0"	14"	20'0"
C275	Thru 10'0"	16"	20'0"
C275	Thru 15'0"	18"	20'0"
C275	Thru 20'0"	20"	15'0"
F265	Thru 9'0"	16"	20'0"
F265	Thru 14'0"	18"	20'0"
F265	Thru 20'0"	20"	15'0"
F265i	Thru 7'0"	16"	20'0"
F265i	Thru 11'0"	18"	20'0"
F265i	Thru 16'0"	20"	11'0"
F265i	Thru 20'0"	22"	9'0"